



# ISOKINETIC PROBES

## STANDARD INTEGRATED STACK SAMPLING PROBES

Our isokinetic probes are realized to make the sampling easier by placing the probe more precisely in the stack emission flow during isokinetic sampling.

Two main types of probes are identified:

- Isokinetic Integrated probes
- Isokinetic Heated Probes

The isokinetic probe is typically composed by a one-block body including the pitot tube, an isokinetic sampling kit in which filterholders and nozzles are included, and

## Main Features

- Low concentration measuring, less than 1 mg/m<sup>3</sup>
- High concentration measuring, greater than 1 g/m<sup>3</sup>
- Maximum temperature: 650 °C . ISO 9096 full compliant
- Gaskets free
- Metal to metal joints
- Complete built in Inox Aisi 316 stainless steel

The isokinetic sampling sometimes has to be done in ducts that have small sections which can lead to practical difficulties when using traditional isokinetic probes.

The solution is the new isokinetic probe named MiniStack.

Thanks to its innovative filterholder, this probe can be used in stacks with section size from 150 mm to 600 mm. The MiniStack probe is composed by a filterholder and a one-block body which includes the Pitot tube, the temperature sensor and the suction tube.



**Ministack Isokinetic Sampling Kit: P/N AC99-104-0000KP**

Description	P/N
1 One-block probe	AC99-104-0001SP
1 Complete filterholder	AC99-104-0010SP
1 Kit n°5 Baskets for glass or quartz wool	AC99-104-9910SP
1 Curve with nozzle diam. 4	AC99-104-9920SP
1 Curve with nozzle diam. 5	AC99-104-9921SP
1 Curve with nozzle diam. 6	AC99-104-9922SP
1 Curve with nozzle diam. 7,6	AC99-104-9923SP
2 Wrench	
1 Tube fitting adapter	
Silicon tube (2 meters)	

## Accessories

### Measuring port


Consists of a thread pipe in carbon steel and a thread cap in zinc plated steel. Mechanically welded or fixed to the stack, it gives a practical measuring and analyzing point.



P/N AC99-104-9902SN

### Slide and lock device


It consists of a chromed plate steel ring and two light alloy shoes. It can be used with the port pipe and on all the thread pipes of 2" with internal diameter over 50 mm.



P/N AC99-104-9901KP

### Flame off adapter

Allows to join the MiniStack's slide and lock device to the flame off cylinder diameter 90 mm or the universal flange TCR Tecora.



P/N AC99-104-9903KP

TCR **Call us!**

+39 02 3664 8635



www.tcrtecora.com



info@tcrtecora.com



Via delle Primule, 16  
Cogliate (MB), 20815, Italy

